


Notification of Change: L-LAS-TB-Scope V5.4.3 to V5.4.4

This document summarises the changes that were made with the software update from **L-LAS-TB-Scope V5.4.3 to V5.4.4**.

New in V5.4.4:

PARA2-TAB:




removed!

REMOVE PARA2\POWER-MODE function element

The POWER-MODE function element is no longer required because of new calibration options (lookup-tables).


CALIB-TAB:



Adaption to new L-LAS-TB-16-AL hardware. 2048 subpixel, working-range = 16.2mm, resolution = 8µm

Additional element in function-list element:
HARDW-TYPE: L-LAS-TB-16-AL
CCD-INT-TYPE: SCAN-LAS-S144

CALIB-TAB:



Adaption to new L-LAS-TB-16-AL hardware. 2048 subpixel, working-range = 16.2mm, resolution = 8µm

Additional element in list-function element:
HARDW-TYPE: L-LAS-TB-16-AL
CCD-INT-TYPE: SCAN-LAS-S144